FABORY



IMPULSE WRENCH 3/8 STRAIGHT RRI-70S

Article number	RRI-70SRED
Brand	-
UBB	500619077836
UNSPSC	27112713
EAN	8717981204069
PKG. of 1	Full Box Only

Technical Parameters

Max. operation pressure	6.3
Tool insertion	3/8 inch
Angle model	No
Idle rotational speed	5000
Air inlet device-sided	R 1/4 inch
Max. loosening torque	47
Max. tightening torque	47
Attract torque adjustable	Yes
Impulse driver	Yes
Max. thread size (metric)	10
Air volume required	372

Standards