FABORY



STRAIGHT GRINDER 150MMX15,9MM TSG-6L

Article number	TSG-6LTOK
Brand	-
UBB	500619093916
UNSPSC	27112708
EAN	8717981035885
PKG. of 1	Full Box Only

Technical Parameters

Rotational speed	6000
Max. operation pressure	6.3
Tool insertion	15.9
Air inlet device-sided	Other
Air volume required	1200

Standards