FABORY



Spiral-Spannstift, geschlitzt, schwer ISO 8752 Federstahl 420-560 HV30 10X100MM

Artikelnummer	39100.100.100
Marke	-
UBB	950359044811
UNSPSC	31163201
EAN	8715492804877
PKG. von 10	Nur komplette Verpackung

Technische Parameter

Durchmesser	10 mm
Länge	100 mm
Material	Federstahl
Material technisch	420-560 HV30
Info	Warning: electroplating of these products may cause hydrogen embrittlement.Dimensions d1 and d2 in above table are before mounting.For pins with a nominal diameter d ≥ 10 mm a single chamfer configuration is optional at the discretion of the manufacturer.V = minimum shear strength, double, in kN.The recommended tolerance class for the accommodating hole diameter d (nominal) is H12.Special features of slotted spring-type straight pins:These

Standards

BS	7060
DIN	1481
ISO	8752
NEN	2458

	pins are used to connect two or more construction elements to each other.They are highly suitable to absorb shear forces.If these pins are employed with bolted joints the below arrangement should be used:

Technische Spezifikation

a (min.)	2
d1 (max.)	10.8
d1 (min.)	10.5
d2 ≈	6.5
D (mm)	10
L (mm)	100
s	2
V	70.16

Technische Zeichnung