FABORY

Slotted countersunk head screw DIN 963 Steel Zinc plated black passivated 4.8 M5X12

Article number	24565.050.012
Brand	-
UBB	950353913334
UNSPSC	31161504
EAN	8715492635426
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	12 mm
Class	4.8
Driving features	Slotted
Head shape	Countersunk head
Material	Steel
Surface treatment	Zinc plated black passivated
Thread	Metric thread

Standards

NEN	≈2370
DIN	963
NF	≈E25-123
BS	≈4183
ISO	≈2009
ASME	≈B18.6.7M

Technical Specification

d-D	M5
Thread length (min.)	25
dk (max.)	9.2
Full thread if L ≤	30
k (max.)	2.5
L (mm)	12
n	1.2
P	0.8
t (min.)	1

Technical Drawing