FABORY

MAXXFAST Self-drilling screw countersunk head cross recessed DIN ≈7504 O-H Stainless steel A2 ST3,9X13MM

Article number	30305.039.013
Brand	-
UBB	500618326275
UNSPSC	31161507
EAN	8715494502047
PKG. of 200	Full Box Only

Technical Parameters

Diameter	3.9 mm
Length	13 mm
Application (metal)	Aluminium
Driving features	Phillips
Head shape	Countersunk head
Material	Stainless steel
Material technical	A2
Thread	Self tapping thread
Info	Full boxes only.

Standards

ISO	≈15482 H
DIN	≈7504-O H

Technical Specification

D (mm)	3.9
dk	8
k	2.6
L (mm)	13
L1	4.5
No. cross recess	2

Technical Drawing