FABORY

Slotted cheese head screw DIN 84 Stainless steel A4 70 M6X90

Article number	55120.060.090
Brand	-
UBB	950353474675
UNSPSC	31161504
EAN	8715492335562
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	90 mm
Class	70
Driving features	Slotted
Head shape	Cylindrical head
Material	Stainless steel
Material technical	A4
Thread	Metric thread

Standards

ISO	≈1207
ASME	≈B18.6.7M
BS	≈4183
NF	≈E25-127
NEN	≈1602
DIN	84

Technical Specification

d-D	M6
Thread length (min.)	38
dk (max.)	10
Full thread if L ≤	40
k (max.)	3.9
L (mm)	90
n	1.6
P	1
t (min.)	1.6

Technical Drawing