

Hexagon head bolt for pressure vessels ISO 4014 Ocel (AD-W7) Pozinkované 5.6 M10X55

Objednací číslo	08751.100.055
Značka	-
UBB	500648335239
UNSPSC	31161620
EAN	8717077214682
BAL. od 100	Pouze celé balení

Technické parametry

Průměr	M10
Délka	55 mm
Třída	5.6
Typ drážky	Šestihran
Tvar hlavy	Šestihranná hlava
Materiál	Ocel (AD-W7)
Směr závitů	Pravý
Povrchová úprava	Pozinkované
Závit	Metrický závit

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10 °C up to +300 °C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a

Standardy

NF	E25-112
ASME	B18.2.3.1M
ISO	4014
DIN	931
NEN	1555

FABORY

certificate EN 10204

3.1 by marking
the fasteners
with the property
class and the
manufacturer's mark.

This recognition is
equally accepted
by Lloyd's Register
Energy.pro tlakové
nádoby

Technická specifikace

b (min.): 125mm $L \leq 200$ mm	32
b (min.): $L > 200$ mm	45
b (min.): $L \leq 125$ mm	26
d-D	M10
k	6.4
L (mm)	55
P	1.5
s	17

Technický náčrt

