



## Assembly set for pressure vessels, fully threaded ISO 4017/4032 Ocel (AD-W7) Žárový zinek 5.6/5.2 pro tlakové nádoby M20X40

|                 |                   |
|-----------------|-------------------|
| Objednací číslo | 08762.200.040     |
| Značka          | -                 |
| UBB             | 500648359650      |
| UNSPSC          | 31161620          |
| EAN             | 8717077245884     |
| BAL. od 25      | Pouze celé balení |

### Technické parametry

|                  |                   |
|------------------|-------------------|
| Průměr           | M20               |
| Délka            | 40 mm             |
| Třída            | 5.6/5.2           |
| Typ drážky       | Šestihran         |
| Tvar hlavy       | Šestihranná hlava |
| Materiál         | Ocel (AD-W7)      |
| Směr závitů      | Pravý             |
| Povrchová úprava | Žárový zinek      |
| Závit            | Metrický závit    |

#### Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to +300°C. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13. Manufacturers included in VdTÜV-

### Standardy

|     |           |
|-----|-----------|
| ISO | 4017/4032 |
|-----|-----------|

Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted by Lloyd's Register Energy.pro tlakové nádoby

## Technická specifikace

|          |      |
|----------|------|
| d-D      | M20  |
| k        | 12.5 |
| L (mm)   | 40   |
| m (max.) | 18   |
| P        | 2.5  |
| s        | 30   |

## Technický náčrt

