



KIPP Indexing plungers without collar, with locking slot Svařitelná nerezová ocel 1.4301, nezpevněná 5MM

Objednací číslo	58624.000.005
Značka	-
UBB	500689892890
UNSPSC	31162807
EAN	4059245017133
BAL. od 3	Pouze celé balení

Technické parametry

D1_MM	12mm
Materiál	Nerezocel
Technický materiál	1.4301

Info

Material: Stainless steel Sleeve 1.4301 weldable. Indexing pin 1.4305. Mushroom knob black grey thermoplastic. Version: Indexing pin not hardened, ground and bright. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually disengaged. The form with locking slot is recommended for applications in where the indexing plungers should remain disengaged over extended

Standardy

periods and the pin prevented from springing back. To weld the indexing plungers we recommend inert gas-shielded welding with TIG welding equipment.

Technická specifikace

D	5
D1	12
D2	21
F1 = springiness beginning in N	5
F2 = springiness end in N	12
F x 30°	1.3
H	5
L1	24
L	43.5

Technický nákres

