

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** MOTIP RAL INDUSTRIAL LACQUER
- **Article number:** 07000 et cetera
- **1.2 Relevant identified uses of the substance or mixture and uses advised against --**
- **Application of the substance / the mixture** Lacquer
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI GmbH
Kurt Vogelsang Strasse 6
D-74855 Haßmersheim
Tel.: +49/6266/75-0
msds@dupli-color.de
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:**
Tel.: +49 6266-75-310
Fax +49 6266-75-362
(Mo - Th 08:00 am - 04:00 pm, Fr 08:00 am - 00:30 pm)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS07

Eye Irrit. 2	H319	Causes serious eye irritation.
STOT SE 3	H336	May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02



GHS07

- **Signal word** Danger
- **Hazard-determining components of labelling:**
acetone
n-butyl acetate
- **Hazard statements**
H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: MOTIP RAL INDUSTRIAL LACQUER

(Contd. of page 1)

· Precautionary statements

- P101 If medical advice is needed, have product container or label at hand.
 P102 Keep out of reach of children.
 P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P211 Do not spray on an open flame or other ignition source.
 P251 Do not pierce or burn, even after use.
 P260 Do not breathe spray.
 P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
 P501 Dispose of contents / container in accordance with regional regulations.

· Additional information:

- EUH066 Repeated exposure may cause skin dryness or cracking.
 Buildup of explosive mixtures possible without sufficient ventilation.

· 2.3 Other hazards**· Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
 · **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

- **Description:** Mixture of substances listed below with nonhazardous additions.

· Dangerous components:

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	acetone Flam. Liq. 2, H225; Eye Irrit. 2, H319; STOT SE 3, H336	25-<50%
CAS: 123-86-4 EINECS: 204-658-1 Index number: 607-025-00-1 Reg.nr.: 01-2119485493-29	n-butyl acetate Flam. Liq. 3, H226; STOT SE 3, H336	20-<25%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	propane Flam. Gas 1, H220; Press. Gas C, H280	10-<12.5%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	butane Flam. Gas 1, H220; Press. Gas C, H280	5-<10%
CAS: 108-65-6 EINECS: 203-603-9 Index number: 607-195-00-7 Reg.nr.: 01-2119475791-29	2-methoxy-1-methylethyl acetate Flam. Liq. 3, H226	5-<10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	isobutane Flam. Gas 1, H220; Press. Gas C, H280	2.5-<5.0%
CAS: 64742-94-5 EINECS: 265-198-5 Index number: 649-424-00-3 Reg.nr.: 01-2119510128-50	Solvent naphtha (petroleum), heavy arom. Asp. Tox. 1, H304	<2.5%

(Contd. on page 3)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: **MOTIP RAL INDUSTRIAL LACQUER**

(Contd. of page 2)

CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25	propan-2-ol ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	<2.5%
CAS: 64742-95-6 EINECS: 265-199-0 Index number: 649-356-00-4 Reg.nr.: 01-2119486773-24	Solvent naphtha (petroleum), light arom. ⚠ Flam. Liq. 3, H226; ⚠ Asp. Tox. 1, H304; ⚠ Aquatic Chronic 2, H411; ⚠ STOT SE 3, H335-H336	≤0.5%

• **Additional information:**

The content of Benzene (EINECS-Nr. 200-753-7) in the ingredients is less than 0,1% (Note P Annex 1 67/548 EU), so the classification as carcinogen need not to apply.

For the wording of the listed risk phrases refer to section 16.

SECTION 4: First aid measures

• **4.1 Description of first aid measures**

- **General information:** Take affected persons out into the fresh air.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, bluspoeder of waterstraal. Grotere brand met waterstraal of met schuim.
Vaten met water afkoelen.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters -**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Do not inhale explosion gases or combustion gases.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Keep away from ignition sources.
Ensure adequate ventilation
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
Do not allow product to reach sewage system or any water course.
- **6.3 Methods and material for containment and cleaning up:**
Do not flush with water or aqueous cleansing agents
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: **MOTIP RAL INDUSTRIAL LACQUER**

(Contd. of page 3)

See Section 13 for disposal information.

SECTION 7: Handling and storage

· 7.1 Precautions for safe handling

Keep away from heat and direct sunlight.

Ensure good interior ventilation, especially at floor level. (Fumes are heavier than air).

Ensure good ventilation/exhaustion at the workplace.

Open and handle receptacle with care.

· Information about fire - and explosion protection:

Do not spray onto a naked flame or any incandescent material.

Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

· 7.2 Conditions for safe storage, including any incompatibilities

· Storage:

· Requirements to be met by storerooms and receptacles:

Store in a cool location.

Observe official regulations on storing packagings with pressurised containers.

· Information about storage in one common storage facility: Not required.

· Further information about storage conditions:

Do not seal receptacle gas tight.

Store in cool, dry conditions in well sealed receptacles.

Protect from heat and direct sunlight.

· Storage class: 2B

· 7.3 Specific end use(s) No further relevant information available.

SECTION 8: Exposure controls/personal protection

· Additional information about design of technical facilities: No further data; see item 7.

· 8.1 Control parameters

· Ingredients with limit values that require monitoring at the workplace:

67-64-1 acetone

WEL Short-term value: 3620 mg/m³, 1500 ppmLong-term value: 1210 mg/m³, 500 ppm

123-86-4 n-butyl acetate

WEL Short-term value: 966 mg/m³, 200 ppmLong-term value: 724 mg/m³, 150 ppm

106-97-8 butane

WEL Short-term value: 1810 mg/m³, 750 ppmLong-term value: 1450 mg/m³, 600 ppm

Carc (if more than 0.1% of buta-1.3-diene)

108-65-6 2-methoxy-1-methylethyl acetate

WEL Short-term value: 548 mg/m³, 100 ppmLong-term value: 274 mg/m³, 50 ppm

Sk

67-63-0 propan-2-ol

WEL Short-term value: 1250 mg/m³, 500 ppmLong-term value: 999 mg/m³, 400 ppm

· Additional information: The lists valid during the making were used as basis.

(Contd. on page 5)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: **MOTIP RAL INDUSTRIAL LACQUER**

(Contd. of page 4)

- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Do not eat, drink, smoke or sniff while working.
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.
- **Respiratory protection:**
Not necessary if room is well-ventilated.
Otherwise, filter class A / P2 or self contained.
- **Protection of hands:**



Protective gloves

Solvent resistant gloves

In case of contact with spray dust protective gloves made of butyl should be used (min. 0.4 mm thick), e.g. KCL Camatril, article no. 898 or similar products

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**
Natural rubber, NR
Butyl rubber, BR
- **Penetration time of glove material**
Butyl rubber gloves with a thickness of 0.4 mm are resistant to:
Acetone: 480 min
Butyl acetate: 60 min
Ethyl acetate: 170 min
Xylene: 42 min
- **Eye protection:** Safety glasses
- **Body protection:** Light weight protective clothing

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Aerosol
Colour:	According to product specification
- **Odour:** Characteristic
- **Odour threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**

Melting point/Melting range:	Undetermined.
Boiling point/Boiling range:	Not applicable, as aerosol.
- **Flash point:** Not applicable, as aerosol.
- **Flammability (solid, gaseous):** Not applicable.
- **Ignition temperature:** 315 °C
- **Decomposition temperature:** Not determined.

(Contd. on page 6)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: **MOTIP RAL INDUSTRIAL LACQUER**

(Contd. of page 5)

· Self-igniting:	Product is not selfigniting.
· Danger of explosion:	In use, may form flammable/explosive vapour-air mixture.
· Explosion limits:	
Lower:	1.2 Vol %
Upper:	13.0 Vol %
· Vapour pressure at 20 °C:	8300 hPa
· Density at 20 °C:	0.77 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
VOC-(EU)	---
	712.4 g/l
· VOC-EU%	91.93 %
· Solids content:	24.9 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity**

· **LD/LC50 values relevant for classification:**

67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
Dermal	LD50	20000 mg/kg (rabbit)

- **Primary irritant effect:**
- **Skin corrosion/irritation** No irritant effect.
- **Serious eye damage/irritation** Irritating effect.
- **Respiratory or skin sensitisation** No sensitising effects known.
- **Additional toxicological information:**

The product shows the following dangers according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:
Irritant

(Contd. on page 7)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: MOTIP RAL INDUSTRIAL LACQUER

Vapours have narcotic effect.

(Contd. of page 6)

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· European waste catalogue

08 01 11*	waste paint and varnish containing organic solvents or other dangerous substances
15 01 04	metallic packaging
15 01 11*	metallic packaging containing a dangerous solid porous matrix (for example asbestos), including empty pressure containers

- **Uncleaned packaging:**
- **Recommendation:** Dispose of packaging according to regulations on the disposal of packagings.

SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR, IMDG, IATA** UN1950
- **14.2 UN proper shipping name**
- **ADR** UN1950 AEROSOLS
- **IMDG** AEROSOLS
- **IATA** AEROSOLS, flammable
- **14.3 Transport hazard class(es)**
- **ADR**
- 
- **Class** 2 5F Gases.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: MOTIP RAL INDUSTRIAL LACQUER

(Contd. of page 7)

· **Label** 2.1· **IMDG, IATA**· **Class** 2.1· **Label** 2.1· **14.4 Packing group**· **ADR, IMDG, IATA** Void· **14.5 Environmental hazards:**· **Marine pollutant:** No· **14.6 Special precautions for user**

Warning: Gases.

· **Danger code (Kemler):**

-

· **EMS Number:**

F-D,S-U

· **14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code**

Not applicable.

· **Transport/Additional information:**· **ADR**· **Limited quantities (LQ)**

1L

· **Excepted quantities (EQ)**

Code: E0

Not permitted as Excepted Quantity

· **Transport category**

2

· **Tunnel restriction code**

D

· **IMDG**· **Limited quantities (LQ)**

1L

· **Excepted quantities (EQ)**

Code: E0

Not permitted as Excepted Quantity

· **UN "Model Regulation":**

UN1950, AEROSOLS, 2.1

* **SECTION 15: Regulatory information**

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture .**· **Information about limitation of use:** Employment restrictions concerning juveniles must be observed.· **Waterhazard class:** Water hazard class 1 (Self-assessment): slightly hazardous for water.· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

* **SECTION 16: Other information**

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H304 May be fatal if swallowed and enters airways.

H319 Causes serious eye irritation.

H335 May cause respiratory irritation.

H336 May cause drowsiness or dizziness.

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.05.2015

Version number 6

Revision: 27.05.2015

Trade name: MOTIP RAL INDUSTRIAL LACQUER

(Contd. of page 8)

H411 Toxic to aquatic life with long lasting effects.· **Contact:** Anwendungstechnik· **Abbreviations and acronyms:***RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)**IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)**ICAO: International Civil Aviation Organisation**ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)**IMDG: International Maritime Code for Dangerous Goods**IATA: International Air Transport Association**GHS: Globally Harmonised System of Classification and Labelling of Chemicals**EINECS: European Inventory of Existing Commercial Chemical Substances**ELINCS: European List of Notified Chemical Substances**CAS: Chemical Abstracts Service (division of the American Chemical Society)**VOC: Volatile Organic Compounds (USA, EU)**LC50: Lethal concentration, 50 percent**LD50: Lethal dose, 50 percent**Flam. Gas 1: Flammable gases, Hazard Category 1**Flam. Aerosol 1: Flammable aerosols, Hazard Category 1**Press. Gas C: Gases under pressure: Compressed gas**Flam. Liq. 2: Flammable liquids, Hazard Category 2**Flam. Liq. 3: Flammable liquids, Hazard Category 3**Eye Irrit. 2: Serious eye damage/eye irritation, Hazard Category 2**STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3**Asp. Tox. 1: Aspiration hazard, Hazard Category 1**Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2*

GB