



Kotvící šroub 12/10

Objednací číslo	96303FIS
Značka	-
UBB	500616705710
UNSPSC	31162101
EAN	4006209963036
BAL. od 20	Pouze celé balení

Technické parametry

Průměr	M12
Délka	61 mm
Klíčové vlastnosti	<p>Functioning - The FAZ II is suitable for pre-positioned and push-through installation; also suitable for stand-off installation under certain conditions. - Prior to installation, place the hexagon nut in the optimal position (the drive-in pin projects by approx. 3 mm out of the hexagon nut). - When applying the torque, the cone bolt is pulled into the expansion clip and expands it against the drill hole wall. - The head embossing offers a simple control of the anchoring. - In the case of series installation, we recommend using the FABS bolt anchor setting tool.</p>

Standardy

Info

do= Nominal
diameter of

drill bit. Min. t_d =
Recommended
drilling depth. h_{ef} =
Effective anchorage
depth. t_{fix} = Grip
range. s = Width
across flats. kN =
Load in kN. The
allowable load is
valid for one single
anchor, at cracked
concrete (tensile
zone) with concrete
class C20/25, incl.
partial safety factor
 $\gamma_f = 1,4$ and if the
 S_{cr} , N and C_{cr} ,
 N are taken in
to account. Final
calculations should
comply with the
complete European
Technical Approval
(ETA), this approval
is also available on
request.

Technická specifikace

Technický náčrtes

