

## Zylinderkerbstifte mit Fase [\*] DIN 1473 Automatenstahl 5X8MM



|               |                          |
|---------------|--------------------------|
| Artikelnummer | 39730.050.008            |
| Marke         | -                        |
| UBB           | 950359660848             |
| UNSPSC        | 31163215                 |
| EAN           | 8715492826152            |
| PKG. von 200  | Nur komplette Verpackung |

### Technische Parameter

|             |                |
|-------------|----------------|
| Durchmesser | 5 mm           |
| Länge       | 8 mm           |
| Material    | Automatenstahl |

#### Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d2 is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d1 (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.


### Standards

|     |       |
|-----|-------|
| DIN | 1473  |
| ISO | ≈8740 |
| NEN | ≈2604 |

### Technische Spezifikation

|        |      |
|--------|------|
| c ≈    | 0.6  |
| d1     | 5    |
| d2 ≈   | 5.25 |
| D (mm) | 5    |
| f ≈    | 2    |

### Technische Zeichnung



|             |      |
|-------------|------|
| L (mm)      | 8    |
| $r \approx$ | 5    |
| Tolerance   | h11  |
| V           | 16.5 |