FABORY



Sechskant-Flachmuttern DIN 439b metrisches Feingewinde DIN 439 2 Rostfreistahl A2 Min.50 M8X0,75 (≠DIN)

Artikelnummer	51092.080.075
Marke	-
UBB	500571314557
UNSPSC	31161727
EAN	8715494139533
PKG. von 200	Nur komplette Verpackung

Technische Parameter

Durchmesser	M8
Klasse	Min.50
Antriebsart	Hexagon
Material	Rostfreistahl
Material technisch	A2
Gewinderichtung	Rechts
Gewinde	Metrisches feines Gewinde
Info	do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor γf= 1,4 and if the

Standards

DIN	439-2
NF	E25-453
ISO	8675
ASME	B18.2.4.5M
NEN	2334-B

Scr, N and Ccr, N are taken in to account.When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request.Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische Spezifikation

d-D	M8
m	4
P	0.75
s	13

Technische Zeichnung

