FABORY



Bolzen 1xd metrisch DIN 938 Rostfreistahl A4 M20X100

Artikelnummer	55280.200.100
Marke	-
UBB	500512328799
UNSPSC	31161610
EAN	8715494303712
PKG. von 25	Nur komplette Verpackung

Technische Parameter

Durchmesser	M20
Länge	100 mm
Material	Rostfreistahl
Material technisch	A4
Gewinderichtung	Rechts
Gewinde	Metrisches Gewinde
Info	ATTENTION: when ordering studs according to this DIN standard the proper designation is d x L,e.g. stud M10X70 - DIN 938, where the working length L = 70 mm and the thread length on the metal end bm = 10 mm. The overall length of the stud is 70 + 10 = 80 mm. The thread length on the nut end b= 26 mm.The thread tolerance class on the metal end is Sk6 according to DIN 13-51, meaning "transition fit", which prevents loosening of the metal end of the studs during

Standards

DIN	938
NF	E25-135

	disassembly.In case this transition fit is not wanted, add "Fo" in the designation. These studs have thread tolerance class 6g on both ends and can be supplied as specials.Studs according to DIN 938 with a metal end ≈1d have many applications, but are mainly intended for use in steel counterparts.

Technische Spezifikation

b	46
bm≈1d	20
b =L-(x+3) up to L≤	55
d-D	M20
L (mm)	100
P	2.5
x	6.3

Technische Zeichnung

