



Sechskant-Flachmuttern DIN 439b metrisches Feingewinde DIN 439 2 Rostfreistahl A2 Min.50 M27X1,50

Artikelnummer	51092.270.150
Marke	-
UBB	950355569928
UNSPSC	31161727
EAN	8715492268273
PKG. von 3	Nur komplette Verpackung

Technische Parameter

Durchmesser	M27
Klasse	Min.50
Antriebsart	Hexagon
Material	Rostfreistahl
Material technisch	A2
Gewinderichtung	Rechts
Gewinde	Metrisches feines Gewinde

Standards

NF	E25-453
NEN	2334-B
ASME	B18.2.4.5M
ISO	8675
DIN	439-2

Info

do = Nominal diameter of drill bit.Min. td = Recommended drilling depth.hef = Effective anchorage depth.tfix = Grip range.s = Width across flats.kN = Load in kN.The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the

Scr, N and Ccr, N are taken in to account. When reduction on spacing and edge distance take place a re-calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technische Spezifikation

d-D	M27
m	13.5
P	1.5
s	41

Technische Zeichnung

