

Bolzen 1xd metrisch DIN 938 Rostfreistahl A4 M20X120



Artikelnummer	55280.200.120
Marke	-
UBB	500512328872
UNSPSC	31161610
EAN	8715494303729
PKG. von 25	Nur komplette Verpackung

Technische Parameter

Standards

Durchmesser	M20	DIN	938
Länge	120 mm	NF	E25-135
Material	Rostfreistahl		
Material technisch	A4		
Gewinderichtung	Rechts		
Gewinde	Metrisches Gewinde		
Info	ATTENTION: when ordering studs according to this DIN standard the proper designation is d x L,e.g. stud M10X70 - DIN 938, where the working length L = 70 mm and the thread length on the metal end bm = 10 mm. The overall length of the stud is 70 + 10 = 80 mm. The thread length on the nut end b= 26 mm.The thread tolerance class on the metal end is Sk6 according to DIN 13-51, meaning "transition fit", which prevents loosening of the metal end of the studs during		

disassembly. In case this transition fit is not wanted, add "Fo" in the designation. These studs have thread tolerance class 6g on both ends and can be supplied as specials. Studs according to DIN 938 with a metal end $\approx 1d$ have many applications, but are mainly intended for use in steel counterparts.

Technische Spezifikation

b	46
$b_m \approx 1d$	20
$b = L - (x + 3)$ up to $L \leq$	55
d-D	M20
L (mm)	120
P	2.5
x	6.3

Technische Zeichnung

