



**Hexagon flange bolt MF  
DIN 6921 Steel Plain 10.9  
M12X1,50X30**

Article number	04135.120.030
Brand	-
UBB	955351424002
UNSPSC	31161620
EAN	8715493858152
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	M12
Length	30 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info      Warning:  
electroplating of  
these products may  
cause hydrogen  
embrittlement.Special  
features of hexagon  
bolts with flange:The  
flange enables built  
up forces to be  
spread over a larger  
area, consequently  
resulting in  
lower surface  
pressure.Large holes  
(oversized) and/or  
tooling holes can  
be covered by the  
flange.A washer is  
not necessary.

**Standards**

DIN	6921
EN	≈1665
ISO	≈4162
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	30
d-D	M12
dc (max.)	26.6
k (max.)	11.5
L (mm)	30
P	1.5
s	16

Technical Drawing

