




Carriage bolt DIN 603 Steel Plain 8.8 M8X50

Article number	08310.080.050
Brand	-
UBB	950351618356
UNSPSC	31161612
EAN	8715492558367
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M8
Length	50 mm
Threaded pitch (P)	1.25
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

ISO	≈8677
DIN	603
BS	≈4933
NEN	≈303

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L200mm	41
b (min.): L≤125mm	22
d-D	M8
dk (max.)	20.65
k (max.)	4.88
L (mm)	50
P	1.25
fn (max.)	5.6
Vn (max.)	8.58

Technical Drawing

