



Hexagon thin nut oversized thread DIN 439 2 Steel Hot dip galvanized 04 M24

Article number	01580.240.001
Brand	-
UBB	950355026655
UNSPSC	31161727
EAN	8715492413543
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	04
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized nuts are manufactured with thread tolerance class 6AZ and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6g before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced disadvantageously

Standards

ISO	4035
DIN	439-2
ASME	B18.2.4.5M
NEN	2334-B
NF	E25-405-1

as the thread will be
protected by the zinc
layer of the mating
part.oversized

Technical Specification

d-D	M24
m	12
P	3
s	36

Technical Drawing

