



**Hexagon flange bolt MF
DIN 6921 Steel Plain 10.9
M10X1,25X70**

Article number	04135.100.070
Brand	-
UBB	955351423848
UNSPSC	31161620
EAN	8715493858138
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	70 mm
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Info Warning:
electroplating of
these products may
cause hydrogen
embrittlement.Special
features of hexagon
bolts with flange:The
flange enables built
up forces to be
spread over a larger
area, consequently
resulting in
lower surface
pressure.Large holes
(oversized) and/or
tooling holes can
be covered by the
flange.A washer is
not necessary.

Standards

ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M
DIN	6921

Technical Specification

b (min.)	26
d-D	M10
dc (max.)	22.3
k (max.)	9.2
L (mm)	70
P	1.25
s	15

Technical Drawing

