



**Prevailing torque type  
hexagon nut, all metal, ISO-  
Metric thread DIN 980V Steel  
Hot dip galvanized 8 ISO  
metric M8**

Article number	12885.080.001
Brand	-
UBB	500648367992
UNSPSC	31161727
EAN	8717077217218
PKG. of 100	Full Box Only

**Technical Parameters**

Diameter	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced

**Standards**

DIN	980-V
NEN	2452
ISO	7042
BS	4929-1
NF	E25-410

disadvantageously  
as the thread will be  
protected by the zinc  
layer of the mating  
part.ISO metric

## Technical Specification

d-D	M8
h (max.)	8
P	1.25
s	13

## Technical Drawing

