



Hexagon flange bolt MF DIN 6921 Steel Plain 10.9 M10X1,25X70

Article number	04135.100.070
Brand	-
UBB	955351423848
UNSPSC	31161620
EAN	8715493858138
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	70
P	1.25
Info	Special features of hexagon bolts with flange: The flange enables built up forces to be spread over a larger area, consequently resulting in lower surface pressure. Large holes (oversized) and/or tooling holes can be covered by the flange. A washer is not necessary.
Class	10.9
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread
Info	Warning: electroplating of these products may

Standards

ASME	≈B18.2.3.4M
EN	≈1665
DIN	6921
ISO	≈4162

cause hydrogen embrittlement.

FABORY
OF COURSE.

Technical Specification

b (min.)	26
d_c (max.)	22.3
k (max.)	9.2
s	15

Technical Drawing

