

Carriage bolt with hexagon nut DIN 603/555 Steel Zinc plated 4.8 M5X25

Article number	08250.050.025
Brand	-
UBB	950351599796
UNSPSC	31161612
EAN	8715492554734
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M5
Length	25 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info
The property class of the corresponding nuts is |4| as a minimum. Depending the supplier material class can differ (4.6 or 4.8)


Standards

BS	≈4933/3692
DIN	603/555
ISO	≈8677/4034
NEN	≈303/697
NF	≈E27-351/E25-402

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
dk (max.)	13.55
k (max.)	3.3
L (mm)	25
m	4
P	0.8
fn (max.)	4.1

Technical Drawing



s

8

Vn (max.)

5.48

