

## Self-clinching through stand off Steel Zinc plated M3X4,18X4

Article number	14422.030.004
Brand	-
UBB	500656717815
UNSPSC	31161816
EAN	8712423025943
PKG. of 1000	Full Box Only

### Technical Parameters


Diameter	M3
Length	4 mm
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Steel self-clinching through stand offs are suitable for use in steel sheet with a maximum hardness of HRB70. For steel sheets with higher hardnesses, rivet bushes are recommended.

### Standards

### Technical Specification

C	4.18
d-D	M3
D	3.2
Hole size	4.2
L (mm)	4
Min. distance sheet edge	6

### Technical Drawing



Min. recommended sheet thickness 1

S  4.8