




Carriage bolt DIN 603 Steel Plain 8.8 M12X45

Article number	08310.120.045
Brand	-
UBB	950351620980
UNSPSC	31161612
EAN	8715492558626
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	45 mm
Threaded pitch (P)	1.75
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

BS	≈4933
ISO	≈8677
NEN	≈303
DIN	603

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
dk (max.)	30.65
k (max.)	6.95
L (mm)	45
P	1.75
fn (max.)	8.75
Vn (max.)	12.7

Technical Drawing

