



Assembly set for pressure vessels ISO 4014/4032 Steel Hot dip galvanized 5.6/5.2 M12X70

| | |
|----------------|---------------|
| Article number | 08753.120.070 |
|----------------|---------------|

| | |
|-------|---|
| Brand | - |
|-------|---|

| | |
|-----|--------------|
| UBB | 500650920951 |
|-----|--------------|

| | |
|--------|----------|
| UNSPSC | 31161620 |
|--------|----------|

| | |
|-----|---------------|
| EAN | 8717077306561 |
|-----|---------------|

| | |
|------------|---------------|
| PKG. of 50 | Full Box Only |
|------------|---------------|

Technical Parameters

| | |
|----------------|-----|
| Diameter (d-D) | M12 |
|----------------|-----|

| | |
|-----------------|----|
| Length (L) (mm) | 70 |
|-----------------|----|

Info

Specific features of fasteners for pressure vessels: Intended for use in pressure vessels, steam appliances, equipment and flange connections at temperatures from -10°C up to $+300^{\circ}\text{C}$. Meets the requirements of AD2000-W7, TRD106 and DIN 267-13 Manufacturers included in VdTÜV-Merkblatt 1253/4 are entitled to replace a certificate EN 10204 3.1 by marking the fasteners with the property class and the manufacturer's mark. This recognition is equally accepted

Standards

| | |
|-----|-----------|
| ISO | 4014/4032 |
|-----|-----------|

by Lloyd's Register
Energy.

FABUKY
Class **OF COURSE** 6/5.2
SETTING THE STANDARD

| | |
|-------------------|--------------------|
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Hot dip galvanized |
| Thread | Metric thread |

Technical Specification

| | |
|---|------|
| b (min.): 125mm $L \leq 200\text{mm}$ | 36 |
| b (min.): $L > 200\text{mm}$ | 49 |
| b (min.): $L \leq 125\text{mm}$ | 30 |
| k | 7.5 |
| m (max.) | 10.8 |
| P | 1.75 |
| s | 18 |

Technical Drawing

