



**Prevailing torque type
hexagon nut, all metal, ISO-
Metric thread DIN 6925 Steel
Hot dip galvanized 8 ISO
metric M20**

Article number	12493.200.001
Brand	-
UBB	500650974909
UNSPSC	31162400
EAN	8717077312029
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M20
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

ISO metric hot dip galvanized nuts are manufactured with thread tolerance class 6H and mate with externally threaded parts (bolts, threaded rods) that are manufactured with thread tolerance class 6az before coating.As the nut thread is tapped after galvanizing the threads are not coated. The corrosion resistance however is not influenced

Standards

ISO	7042
DIN	6925

disadvantageously
as the thread will be
protected by the zinc
layer of the mating
part.ISO metric

Technical Specification

d-D	M20
h	20
P	2.5
s	30

Technical Drawing

