

MAXXFAST Hammerset
anchor Steel Zinc plated M8



Article number	30575.080.001
Brand	-
UBB	500619771339
UNSPSC	31162101
EAN	8715494136310
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	D-MAXX

Info	do= Nominal diameter of drill bitdw= Diameter of clearance hole in the fixtureh1= Depth of drilled hole to deepest pointhc= Minimal thickness of concrete elemente = Bolt length to be threadedSmin.= Minimal spacingCmin.= Minimal edge distanceNrec= Recommended load in kNTinst= Tightening torque in NmThe allowable load (Nrec) is valid for one single anchor, at non-cracked concrete (pressure zone) with concrete class C20/25, incl. partial safety factor $\gamma_f= 1,4$
------	---

Standards

Technical Specification

Cmin.	105
d-D	M8
do	10
dw	9
e (max.)	13
e (min.)	8
h1	33
hc	100
L (mm)	30
Nrec	2.74
Smin.	90
Tinst	11

Technical Drawing

