



## Spring-type straight pin slotted, heavy duty, stainless spring steel DIN ≈1481 Stainless spring steel 3,5X36MM

Article number	51428.035.036
Brand	-
UBB	500635839391
UNSPSC	31163201
EAN	8717077785731
PKG. of 1000	Full Box Only

### Technical Parameters

Diameter	3.5 mm
Length	36 mm
Material	Stainless spring steel

#### Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter  $d \geq 8$  mm a single chamfer configuration is optional at the discretion of the manufacturer. The recommended tolerance class for the accommodating hole diameter  $d$  (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each other. They are highly suitable to absorb shear forces. If these

### Standards

NEN	≈2458
ISO	≈8752
BS	≈7060
DIN	≈1481

**FABORY** pins are employed  
with bolted joints the  
below arrangement  
should be used:

### Technical Specification

a	0.6
d1 (max.)	4
d1 (min.)	3.8
d2 ≈	2.3
D (mm)	3.5
L (mm)	36
s	0.75

### Technical Drawing

