



Disc spring for critical applications Steel Ck 67 Werkstoffnr. 1.1231 Phosphated 28X10,2X1,0MM

| | |
|----------------|---------------|
| Article number | 36450.290.010 |
| Brand | - |
| UBB | 950357495148 |
| UNSPSC | 31161811 |
| EAN | 8715492762221 |
| PKG. of 50 | Full Box Only |

Technical Parameters

| | |
|--------------------|---------------------------|
| Diameter | 10.2 mm |
| d _e | 28 |
| d _i | 10.2 |
| Material | Steel |
| Material technical | Ck 67 Werkstoffnr. 1.1231 |
| Outer diameter | 28 |
| Surface treatment | Phosphated |

Info

Warning:
electroplating of these products may cause hydrogen embrittlement. Disc springs are mostly used in critical applications with safety first. Similar applications can be found in for example safety torque limiter clutches, hinge stiffeners and applications of constant roll pressure. Because of the right combination c.q. stacking of the disc

Standards

springs the elasticity and/or deflection can be dosed accurately. The technical specifications of these disc springs meet the highest expectations with reference to the static and dynamic load. They exceed the requirements of DIN 2093. Material group 1: $t \leq 1,25$ from steel Ck 67. Material group 2: $1,25 \leq t \leq 6,0$ from steel 50 Cr V4. Material group 3: $6,0 < t \leq 14,0$ from steel 50 Cr V4. Fatigue fractures can be largely prevented because the disc springs of material group 2 and 3 have machined edges. F = spring force in Newton at a deflection $s \approx 0,75 h_0$ ($h_0 = L_0 - t$). For the calculation of disc springs, see DIN 2092. Extensive technical data available on request.

Technical Specification

| | |
|-----------|------|
| di (H12) | 10.2 |
| D (mm) | 10.2 |
| F | 1130 |
| l0 | 1.9 |
| t | 1 |
| Thickness | 1 |

Technical Drawing

