

Spring-type straight pin slotted, heavy duty ISO 8752 Spring steel 420-560 HV30 Zinc plated 3X14MM



Article number	39105.030.014
----------------	---------------

Brand	-
-------	---

UBB	500649079885
-----	--------------

UNSPSC	31163201
--------	----------

EAN	8717077256408
-----	---------------

PKG. of 200	Full Box Only
-------------	---------------

Technical Parameters

d (nom.)	3
----------	---

Diameter (mm)	3
---------------	---

Length (L) (mm)	14
-----------------	----

Info

Dimensions d1 and d2 in above table are before mounting. For pins with a nominal diameter $d \geq 10$ mm a single chamfer configuration is optional at the discretion of the manufacturer.

V = minimum shear strength, double, in kN. The recommended tolerance class for the accommodating hole diameter d (nominal) is H12. Special features of slotted spring-type straight pins: These pins are used to connect two or more construction elements to each other. They are highly suitable to

Standards

DIN	1481
-----	------

ISO	8752
-----	------

BS	7060
----	------

absorb shear forces.
 If these pins are employed with bolted joints the below arrangement should be used:

Material	Spring steel
Material technical	420-560 HV30
Surface treatment	Zinc plated

Technical Specification

a (min.)	0.5
d ₁ (max.)	3.5
d ₁ (min.)	3.3
d ₂ ≈	2.1
s	0,6
V	6.32

Technical Drawing

