

## Hexagon head bolt DIN 931 Stainless steel A4 Min.50 M14X120

|                |               |
|----------------|---------------|
| Article number | 55000.140.120 |
| Brand          | -             |
| UBB            | 951351772854  |
| UNSPSC         | 31161620      |
| EAN            | 8715492320995 |
| PKG. of 10     | Full Box Only |

### Technical Parameters

|                    |                                                                                      |
|--------------------|--------------------------------------------------------------------------------------|
| Diameter           | M14                                                                                  |
| Length             | 120 mm                                                                               |
| Class              | Min.50                                                                               |
| Driving features   | Hexagon                                                                              |
| Head shape         | Hexagon head                                                                         |
| Material           | Stainless steel                                                                      |
| Material technical | A4                                                                                   |
| Thread direction   | Right                                                                                |
| Thread             | Metric thread                                                                        |
| Info               | Sizes with a diameter M20 and sizes with a length 8xd are minimal property class 50. |

### Standards

|      |            |
|------|------------|
| ISO  | 4014       |
| ASME | B18.2.3.1M |
| DIN  | 931        |
| NF   | E25-112    |
| NEN  | 1555       |

### Technical Specification

|                           |     |
|---------------------------|-----|
| b (min.):<br>125mmL≤200mm | 40  |
| b (min.): L200mm          | 53  |
| b (min.): L≤125mm         | 34  |
| d-D                       | M14 |
| k                         | 8.8 |
| L (mm)                    | 120 |
| P                         | 2   |
| s                         | 22  |

### Technical Drawing

