

Grooved pin, half length taper grooved DIN 1472 Free-cutting steel 1,5X16MM



Article number	39720.015.016
Brand	-
UBB	950359132350
UNSPSC	31163215
EAN	8715492824936
PKG. of 250	Full Box Only

Technical Parameters

d ₁	1.5
Diameter (mm)	1.5
Length (L) (mm)	16

Standards

ISO	8745
DIN	1472

Info

V = minimum shear strength double shear in kN (valid for steel pins only). Diameter d₂ is the diameter over the grooved edges (valid for steel pins only). The recommended tolerance class for the accommodating hole diameter d_# (nominal) is H11. The nominal length (L, tolerance class js15) does not include the rounded ends.

Material	Free-cutting steel
----------	--------------------

Technical Specification

c ≈	0.2
d ₂ ≈	1.6
r ≈	1.5
Tolerance	h9

Technical Drawing

FABORY
OF COURSE.
SETTING THE STANDARD
IN FASTENING SOLUTIONS

