



**KIPP Indexing plungers
with threaded pin, without
collar, without locknut Metric
fine thread Stainless steel
1.4305, pin not hardened
4MM**

Article number	58617.000.004
Brand	-
UBB	500689889011
UNSPSC	31162807
EAN	4059245016433
PKG. of 4	Full Box Only

Technical Parameters

D1_MM	8mm
Material	Stainless steel
Material technical	1.4305

Thread	Metric fine thread
--------	--------------------

Info	Material: Indexing pin hardened: Threaded sleeve 1.4305. Indexing pin 1.4034. Indexing pin not hardened: Threaded sleeve 1.4305. Indexing pin 1.4305. Mushroom knob 1.4305, electrolytic-polish. Version: Bright. Indexing pin ground. Note: Indexing plungers are used to prevent any change in locking position due to lateral forces. A new locking position can only be set after the pin has been manually
------	---

Standards

disengaged. A screw-in washer can be supplied to help screw the indexing plungers in. The washer slides beneath the disengaged mushroom knob so that the follower pins engage in the slot.

Technical Specification

D	4
D1	8
D2	3
F1 = springiness beginning in N	6
F2 = springiness end in N	12
F x 30°	1
H	4
L1	21
L2	7
L	32
P	1

Technical Drawing

