



Split pin (cotter pin) DIN 94 Stainless steel A2 5X71MM

| | |
|----------------|---------------|
| Article number | 51700.050.071 |
| Brand | - |
| UBB | 500621791846 |
| UNSPSC | 31163204 |
| EAN | 8715494512930 |
| PKG. of 50 | Full Box Only |

Technical Parameters

| | |
|--------------------|-----------------|
| Diameter | 5 mm |
| Length | 71 mm |
| Material | Stainless steel |
| Material technical | A2 |

Standards

| | |
|-----|---------|
| ISO | 1234 |
| NEN | 182 |
| NF | E25-774 |
| DIN | 94 |

| | |
|------|--|
| Info | Other types of stainless steel than specified (but with equal properties) may be supplied at the discretion of the manufacturer. The shape of the split pin ends are at the manufacturer's discretion. For stainless steel split pins the type of austenitic stainless steel is at the manufacturer's discretion and may vary from the steel types stated in ISO 3506. The recommended tolerance class for the accommodating hole diameter d (nominal) is H13 for $d \leq 1,2$ mm and H14 for bigger diameters. The tolerance class of |
|------|--|

the nominal length
(L) is js17.

FABORY

Technical Specification

| | |
|----------|-----|
| a (max.) | 4 |
| b ≈ | 10 |
| c (max.) | 9.2 |
| c (min.) | 8 |
| d (min.) | 4.4 |
| D (mm) | 5 |
| L (mm) | 71 |
| d (max.) | 4.6 |

Technical Drawing

