



Machine screw pan head UNC asme B18.6.3 ASME B18.6.3 Stainless steel A2 (AISI 304/18-8) #2-56X3/4

Article number	U51122.008.0075
Brand	-
UBB	500625001168
UNSPSC	31161504
EAN	8717077793446
PKG. of 100	Full Box Only

Technical Parameters

Diameter	NO.2
Length	3/4 Inch
Driving features	Phillips
Head shape	Pan head
Material	Stainless steel
Material technical	ASTM F837 304
Thread direction	Right
Thread	Unified National Coarse
Threads per inch	56

Info
Screws with diameter \leq No.5 and length \leq 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min. Screws with diameter No.5 and length \leq 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min.

Standards

ASME	B18.6.3
------	---------

Technical Specification

A (max.)	0.167
H (max.)	0.062

Technical Drawing

FABORY

