



## Hexagon socket set screw with cup point DIN 916 Stainless steel A4 M12X16

|                |               |
|----------------|---------------|
| Article number | 55260.120.016 |
| Brand          | -             |
| UBB            | 952351081569  |
| UNSPSC         | 31161518      |
| EAN            | 8715492339249 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |                                                                                                    |
|--------------------|----------------------------------------------------------------------------------------------------|
| Diameter           | M12                                                                                                |
| Length             | 16 mm                                                                                              |
| Driving features   | Hexagon socket                                                                                     |
| Material           | Stainless steel                                                                                    |
| Material technical | A4                                                                                                 |
| Thread direction   | Right                                                                                              |
| Point              | Cup                                                                                                |
| Thread             | Metric thread                                                                                      |
| Info               | These set screws are designed for pressure loads and are not suitable for tensile- or shear loads. |

### Standards

|      |          |
|------|----------|
| ISO  | 4029     |
| ASME | B18.3.6M |
| BS   | 4168-5   |
| NEN  | 2343     |
| DIN  | 916      |
| NF   | E27-183  |

### Technical Specification

|          |      |
|----------|------|
| d-D      | M12  |
| dv       | 8    |
| L (mm)   | 16   |
| P        | 1.75 |
| s        | 6    |
| t (min.) | 4.8  |

### Technical Drawing

