



**Machine screw oval
countersunk UNC asme
B18.6.3 ASME B18.6.3
Stainless steel A2 (AISI
304/18-8) 5/16-18X2.1/2**

| | |
|----------------|-----------------|
| Article number | U51320.031.0250 |
| Brand | - |
| UBB | 500625050322 |
| UNSPSC | 31161504 |
| EAN | 8717077792722 |
| PKG. of 10 | Full Box Only |

Technical Parameters

| | |
|--------------------|----------------------------|
| Diameter | 5/16 Inch |
| Length | 2.1/2 Inch |
| Driving features | Phillips |
| Head shape | Countersunk oval |
| Material | Stainless steel |
| Material technical | ASTM F837 304 |
| Thread direction | Right |
| Thread | Unified National Coarse |
| Threads per inch | 18 |

| | |
|------|---|
| Info | Screws with diameter ≤ No.5 and length ≤ 1.1/8 inch are fully threaded, longer screws are threaded 1 inch min.Screws with diameter No.5 and length ≤ 2 inch are fully threaded, longer screws are threaded 1.1/2 inch min. |
|------|---|

Standards

| | |
|------|---------|
| ASME | B18.6.3 |
|------|---------|

Technical Specification

| | |
|----------|-------|
| A (max.) | 0.597 |
|----------|-------|

Technical Drawing

| | |
|------------------|-------|
| C | 0.099 |
| H (max.) | 0.191 |
| No. cross recess | 4 |

