

**Safety data sheet
according to 1907/2006/EC, Article 31**

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** Eco Cleaner
- **Int. code:** SP122
- **UFI:** U030-G0D1-P00H-UAN6
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Cleaning agent/ Cleaner
- **Product intended for:** Trade users / technical specialists.
- **Uses advised against**
- **1.3 Manufacturer/Supplier:**
Dreumex B.V.
Dommelstraat 1
5347 JK, Oss, The Netherlands
Postal box 681, 5340 AR, Oss, The Netherlands
Tel: +31 (0)412-406 506
Fax : +31 (0)412-406 509
E-mail address: mail@dreumex.com
Website: www.dreumex.com
- **1.4 Emergency telephone number:** Dreumex B.V. +31 (0)412-406 506

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



corrosion

Eye Dam. 1 H318 Causes serious eye damage.



Skin Irrit. 2 H315 Causes skin irritation.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the GB CLP regulation.
- **Hazard pictograms** GHS05
- **Signal word** Danger
- **Hazard-determining components of labelling:**
2-aminoethanol
C10 Alcohol ethoxylate
sulfuric acid, mono-C12-C14-alkyl esters, sodium salt
- **Hazard statements**
H315 Causes skin irritation.
H318 Causes serious eye damage.
- **Precautionary statements**
P264 Wash thoroughly after handling.
P280 Wear protective gloves / eye protection / face protection.

(Contd. on page 2)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 1)

- P302+P352 IF ON SKIN: Wash with plenty of water.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P310 Immediately call a POISON CENTER/doctor.
 P332+P313 If skin irritation occurs: Get medical advice/attention.
 P362+P364 Take off contaminated clothing and wash it before reuse.

- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

- **3.2 Mixtures**
- **Description:** Mixture of substances listed below with nonhazardous additions.

Dangerous components:

CAS: 141-43-5 EINECS: 205-483-3 Reg.nr.: 01-2119486455-28-XXXX	2-aminoethanol ⚠ Skin Corr. 1B, H314; Eye Dam. 1, H318; ⚠ Acute Tox. 4, H302; Acute Tox. 4, H312; Acute Tox. 4, H332; STOT SE 3, H335; Aquatic Chronic 3, H412 Specific concentration limit: STOT SE 3; C ≥ 5 %	≥3-<5%
CAS: 5949-29-1 EINECS: 201-069-1 Reg.nr.: 01-2119457026-42-XXXX	citric acid ⚠ Eye Irrit. 2, H319; STOT SE 3, H335	≤2.5%
CAS: 160875-66-1 Polymer	C10 Alcohol ethoxylate ⚠ Eye Dam. 1, H318	≥1-≤2.5%
CAS: 85586-07-8 Reg.nr.: 01-2119489463-28-XXXX	sulfuric acid, mono-C12-C14-alkyl esters, sodium salt ⚠ Eye Dam. 1, H318; ⚠ Acute Tox. 4, H302; Skin Irrit. 2, H315; Aquatic Chronic 3, H412	≥1-<2.5%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **General information:** Immediately remove any clothing soiled by the product.
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:**
Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:**
Rinse out mouth.
Do not induce vomiting; call for medical help immediately.
- **4.2 Most important symptoms and effects, both acute and delayed**
No further relevant information available.

(Contd. on page 3)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 2)

- **4.3 Indication of any immediate medical attention and special treatment needed**
 No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**
 No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** In case of insufficient ventilation, wear suitable respiratory equipment.
- **Additional information** Cool endangered receptacles with water spray.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
 Wear protective equipment. Keep unprotected persons away.
 Wear protective clothing.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
 Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
 Use neutralising agent.
 Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections**
 See Section 7 for information on safe handling.
 See Section 8 for information on personal protection equipment.
 See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
 Protect from frost.
 Keep container tightly sealed.
 Use only polymer packing for storage and sending.
- **Storage class: -**
- **7.3 Specific end use(s)** No further relevant information available.

GB

(Contd. on page 4)

**Safety data sheet
according to 1907/2006/EC, Article 31**

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 3)

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Appropriate engineering controls** No further data; see item 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Avoid contact with the skin.
Avoid contact with the eyes and skin.
- **Respiratory protection:** Not necessary if room is well-ventilated.
- **Hand protection**



Protective gloves

- **Material of gloves** Synthetic rubber gloves
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye/face protection**



Tightly sealed goggles

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Physical state** Fluid
- **Colour:** Green
- **Odour:** Characteristic
- **Odour threshold:** Not determined.
- **Melting point/freezing point:** Undetermined.
- **Boiling point or initial boiling point and boiling range** 100 °C
- **Flammability** Not applicable.
- **Lower and upper explosion limit**
- **Lower:** Not determined.
- **Upper:** Not determined.
- **Flash point:** Not applicable.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 4)

· Decomposition temperature:	Not determined.
· pH at 20 °C	11.3
· Viscosity:	
· Kinematic viscosity	Not determined.
· Dynamic:	Not determined.
· Solubility	
· water:	Fully miscible.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure at 20 °C:	23 hPa
· Density and/or relative density	
· Density at 20 °C:	1.02932 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.

· 9.2 Other information	
· Appearance:	
· Form:	Fluid
· Important information on protection of health and environment, and on safety.	
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Not determined
· Solvent content:	
· Organic solvents:	3.0 %
· Water:	84.9 %
· Solids content:	4.4 %
· Change in condition	
· Evaporation rate	Not determined.

· **Information with regard to physical hazard classes**

· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Void
· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void

(Contd. on page 6)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 5)

· Desensitised explosives

Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**

· **Acute toxicity**

- **LD/LC50 values relevant for classification:**

141-43-5 2-aminoethanol

Oral	LD50	1,089 mg/kg (rat)
Dermal	LD50	2,504 mg/kg (rat)
Inhalative	LC50/4 h	>1.48 mg/l (rat)

· **Skin corrosion/irritation**

Irritation.

Causes skin irritation.

- **Serious eye damage/irritation** Causes serious eye damage.

· **11.2 Information on other hazards**· **Endocrine disrupting properties**

None of the ingredients is listed.

SECTION 12: Ecological information· **12.1 Toxicity**· **Aquatic toxicity:****141-43-5 2-aminoethanol**

EC50/48h	65 mg/l ((Daphnia) Daphnia magna)
LC50/96h	349 mg/l ((Fish) Cyprinus carpio)
EC50	>1,000 mg/l (activated sludge)
NOEC/21d	0.85 mg/l ((Daphnia) Daphnia magna)
ErC50/72h	2.5 mg/l ((Algae) Pseudokirchneriella subcapitata)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 6)

- **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

- **12.6 Endocrine disrupting properties**

The product does not contain substances with endocrine disrupting properties.

- **12.7 Other adverse effects**

- **Additional ecological information:**

- **General notes:**

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Must not reach sewage water or drainage ditch undiluted or unneutralised.

Rinse off of bigger amounts into drains or the aquatic environment may lead to increased pH-values.

A high pH-value harms aquatic organisms. In the dilution of the use-level the pH-value is considerably reduced, so that after the use of the product the aqueous waste, emptied into drains, is only low water-dangerous.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation** Disposal must be made according to official regulations.

- **Uncleaned packaging:**

- **Recommendation:** Disposal must be made according to official regulations.

- **Recommended cleansing agents:** Water, if necessary together with cleansing agents.

SECTION 14: Transport information

- **14.1 UN number or ID number**

- **ADR, ADN, IMDG, IATA** Void

- **14.2 UN proper shipping name**

- **ADR, ADN, IMDG, IATA** Void

- **14.3 Transport hazard class(es)**

- **ADR, ADN, IMDG, IATA**

- **Class** Void

- **14.4 Packing group**

- **ADR, IMDG, IATA** Void

- **14.5 Environmental hazards:**

- **Marine pollutant:** No

- **14.6 Special precautions for user**

Not applicable.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 7)

· 14.7 Maritime transport in bulk according to IMO instruments	Not applicable.
· Transport/Additional information:	Not dangerous according to the above specifications.
· UN "Model Regulation":	Void

SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**

· Directive 2012/18/EU

· **Named dangerous substances - ANNEX I** None of the ingredients is listed.

· **DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**

None of the ingredients is listed.

· **Annex I - RESTRICTED EXPLOSIVES PRECURSORS (Upper limit value for the purpose of licensing under Article 5(3))**

None of the ingredients is listed.

· **Annex II - REPORTABLE EXPLOSIVES PRECURSORS**

None of the ingredients is listed.

· **Regulation (EC) No 273/2004 on drug precursors**

None of the ingredients is listed.

· **Regulation (EC) No 111/2005 laying down rules for the monitoring of trade between the Community and third countries in drug precursors**

None of the ingredients is listed.

· **National regulations:**

The product is subject to be labeled according with the prevailing version of the regulations on hazardous substances.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

The aerosol is an aerosol with a two-compartment system. The product, without propellant, is contained in the inner compartment (bag of foil). Between the bag (with product) and the can is pressurized air, which puts pressure on the bag and propels the product outside when the nozzle is pushed.

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

EU Regulation on aerosols 75/324/EC, 1994/1/EC and 2008/47/EC

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

(Contd. on page 9)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 21.04.2023

Version number 2

Revision: 21.04.2023

Trade name: Eco Cleaner

(Contd. of page 8)

H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H332 Harmful if inhaled.
H335 May cause respiratory irritation.
H412 Harmful to aquatic life with long lasting effects.

· **Department issuing SDS:**

· **Date of previous version:** 09.05.2019

· **Abbreviations and acronyms:**

ADR: Accord relatif au transport international des marchandises dangereuses par route

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Acute Tox. 4: Acute toxicity – Category 4

Skin Corr. 1B: Skin corrosion/irritation – Category 1B

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· **Sources** <http://echa.europa.eu>

· *** Data compared to the previous version altered.**

GB