

扫微信二维码
关注谱尼测试

Pony Testing International Group

Report No.: MNIZDMWX92683716

MSDS Report

Sample Description
& Model

Li-ion Battery 14650

Applicant

XIAMEN WISETECH OPTOELECTRONIC CO.,LTD

Address

C4, No.96 XiangXing Road, Xiamen Torch (Xiang'an)
Industrial Zone, Xiamen, China



微信扫一扫，使用小程序 小程序扫一扫，在线验证

No.: MNIZDMWX92683716

Code: e35139



北京实验室: (010)82618116

上海实验室: (021)64851999

青岛实验室: (0532)88706866

深圳实验室: (0755)26050909

天津实验室: (022)27360730

苏州实验室: (0512)62997900

长春实验室: (0431)85150908

大连实验室: (0411)87336618

哈尔滨实验室: (0451)88104651

郑州实验室: (0371)69350670

新疆实验室: (0991)6684186

石家庄实验室: (0311)85376660

西安实验室: (029)89608785

呼和浩特实验室: (0471)3450025

杭州实验室: (0571)87219096

宁波实验室: (0574)87736499

武汉实验室: (027)83997127

合肥实验室: (0551)63843474

广州实验室: (020)89224310

厦门实验室: (0592)5568048

成都实验室: (028)87702708

声 明
Statement

1. 本证明/报告的结论仅对委托方所送样品负责。
The conclusion of the certificate/report is responsible for the provided sample only.
2. 委托方必须如实提供样品, 申报和声明资料, 并保证与实际相符, 否则由委托方承担由此导致的全部后果和责任。
The applicant shall provide accurately and truly the description and statement of the sample, shall guarantee to match the sample and real situation which they provided and declared. Otherwise the application shall bear any relevant consequences and responsibility.
3. 如委托方提供的样品及相关资料存在虚假、伪造等情形, 所造成的全部后果和责任由委托方承担。
In case the sample and documents provided involved in the situation of fake and forgery, any consequences and responsibility caused by this shall be undertaken by applicant.
4. 本证明/报告全部或部分复制、私自转让、盗用、冒用、涂改或以其它任何形式篡改的均属无效, 本单位将对上述行为追究其相应的法律责任。
The certificate/report can not be copied in whole or part, the copied version is invalid. The certificate is invalid in case of illegal transfer, reproduction, embezzlement, imposture, modification or any altering. PONY shall investigate the applicant's legal liability accordingly.
5. 本证明/报告不考虑国家及经营人差异。
The certificate/report takes no account of the differences of countries and applicants.
6. 本单位有权在完成证明/报告后处理委托方所送样品。
PONY has the right to dispose the provided sample after approval of the certificate/report.

▲ 防伪说明:

- (1) 报告编号是唯一的;
- (2) 报告采用特制防伪纸张印制, 纸张表面带有“PONY”防伪纹路, 该防伪纹路不支持复印, 即复制件不会带有“PONY”防伪纹路;
- (3) 报告采用的防伪纸张内部亦加带有高科技“PONY”防伪水印, 只有在验钞机等紫外线照射下方可显出无色荧光防伪字样。



扫二维码
关注谱尼测试

www.ponytest.com

Hotline 400-819-5688

北京实验室: (010)82618116
上海实验室: (021)64851999
青岛实验室: (0532)88706866
深圳实验室: (0755)26050909
天津实验室: (022)27360730
苏州实验室: (0512)62997900

长春实验室: (0431)85150908
大连实验室: (0411)87336618
哈尔滨实验室: (0451)88104651
郑州实验室: (0371)69350670
新疆实验室: (0991)6684186

石家庄实验室: (0311)85376660
西安实验室: (029)89608785
呼和浩特实验室: (0471)3450025
杭州实验室: (0571)87219096
宁波实验室: (0574)87736499

武汉实验室: (027)83997127
合肥实验室: (0551)63843474
广州实验室: (020)89224310
厦门实验室: (0592)5568048
成都实验室: (028)87702708



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 1 of 11

Material Safety Data Sheet

Reference to ST/SG/AC.10/30/Rev.7 (GHS)

Section 1 - Chemical Product and Company Identification

Chemical Product Identification

Sample Description: Li-ion Battery

Sample Model: 14650

Recommended Uses: N/A

Restrictions on Use: N/A

Supplier Name: SHENZHEN BOFUNENG BATTERY CO., LTD

Address: A Building Chun yang Industrial park, Zhugushi Road Wulian community Long Cheng Street, Longgang district, Shenzhen China

Phone Number: 0755-84642975

FAX: 0755-84642732

E-mail: aijuan_1425@126.com

Emergency Phone Number: 0755-84642975

Section 2 - Hazards Identification

Emergency overview: This product is a battery. Intended use of the product should not result in exposure to the chemical substance. In case of rupture the below hazards exist.

Classification according to GHS

Acute toxicity, oral (4)

Skin corrosion/irritation (2)

Serious eye damage/eye irritation (2A)

Specific target organ toxicity, single exposure; Respiratory tract irritation (3)

Label elements

Hazard pictogram(s):

Signal word:

Warning

Hazard statement(s):

H302 Harmful if swallowed

H315 Causes skin irritation



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 2 of 11

H319 Causes serious eye irritation

H335 May cause respiratory irritation

Precautionary statement(s):

Prevention:

P264 Wash skin and clothing thoroughly after handling.

P270 Do not eat, drink or smoke when using this product.

P280 Wear protective gloves, protective clothing, eye protection, face protection.

P261 Avoid breathing dust, fume, gas, mist, vapours, spray.

P271 Use only outdoors or in a well-ventilated area.

Response:

P301 + P312 IF SWALLOWED: Call a POISON CENTER if you feel unwell.

P330 Rinse mouth.

P302 + P352 IF ON SKIN: Wash with plenty water.

P321 Specific treatment (See additional emergency instructions).

P333 + P313 If skin irritation or rash occurs: Get medical advice.

P362 + P364 Take off contaminated clothing and wash it before reuse.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337 + P313 If eye irritation persists: Get medical advice.

P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P312 Call a POISON CENTER, if you feel unwell.

Storage

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

P405 Store locked up.

Disposal:

P501 Send contents to approved waste treatment plants.

Other hazards

Physical and chemical hazards: See Section 10

Human health hazards: See Section 11

Environmental hazards: See Section 12

Section 3 – Composition/Information on Ingredients

Chemical characterization: Mixture



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 3 of 11

Chemical Composition	CAS No.	EC#	Weight (%)
Lithium Ni-Co-Mn Oxid	---	---	39.60
Aluminium	7429-90-5	231-072-3	5.56
Polyvinylidene fluoride resin	24937-79-9	607-458-6	1.15
Graphite	7782-42-5	231-955-3	23.2
Copper	7440-50-8	231-159-6	9.8
Rubber, styrene-butadiene, fume	61789-96-6	612-382-1	1.78
Polyethylene	9002-88-4	618-339-3	0.06
Polypropylene	9003-07-0	618-352-4	0.78
Phosphate(1-), hexafluoro-, lithium	21324-40-3	244-334-7	15.35
1,3-Dioxolan-2-one	96-49-1	202-510-0	2.72

Section 4 - First Aid Measures

Description of first aid measures

General information No special measures required.

After eye contact

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

After skin contact

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

After inhalation

Remove victim to fresh area. Administer artificial respiration if breathing is difficult. Seek medical attention.

After swallowing

Do not induce vomiting. Get medical attention.

Personal protective equipment for first-aid responders: No data available.

Most important symptoms/effects, acute and delayed: No data available.

Indication of immediate medical attention and special treatment needed: Treat symptomatically.



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 4 of 11

Section 5 - Fire Fighting Measures

Suitable extinguishing media:

Small Fire: Dry chemical, CO₂, water spray or regular foam. Large Fire: Water spray, fog or regular foam. Move containers from fire area if you can do it without risk.

Unsuitable extinguishing media:

No data available.

Specific Hazards arising from the chemical:

Special hazards arising from the substance or mixture

Battery may burst and release hazardous decomposition products when exposed to a fire situation. Lithium ion batteries contain flammable electrolyte that may vent, ignite and produce sparks when subjected to high temperature(>150°C(302°F)), when damaged or abused (e.g. mechanical damage or electrical overcharging); may burn rapidly with flare-burning effect; may ignite other batteries in close proximity.

Specific protective actions for fire-fighters:

Wear positive pressure self-contained breathing apparatus (SCBA). Structural firefighters' protective clothing will only provide limited protection.

Section 6 - Accidental Release Measures

Personal precautions:

As an immediate precautionary measure, isolate spill or leak area for at least 25 meters (75 feet) in all directions. Keep unauthorized personnel away. Stay upwind, uphill and/or upstream. Ventilate closed spaces before entering. Large Spill: Consider initial downwind evacuation for at least 100 meters (330 feet).

Protective equipment:

No data available.

Emergency procedures:

ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Do not touch or walk through spilled material. Absorb with earth, sand or other non-combustible material. Leaking batteries and contaminated absorbent material should be placed in metal containers.

Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

Methods and materials for containment and cleaning up:

For all waste handling must refer to United Nations, National and Local Regulations for disposal.



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 5 of 11

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

Section 7 - Handling and Storage

Precautions for safe handling:

Avoid short circuiting the battery. Avoid mechanical damage of the battery. Do not open or disassemble. Batteries may explode or cause burns, if disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect polarity. Avoid all personal contact, including inhalation. Wear protective clothing when risk of exposure occurs. Use in a well-ventilated area. Prevent concentration in hollows and sumps.

Conditions for safe storage, including any incompatibilities:

Store in a cool, dry, well-ventilated place. Keep away from heat, avoiding the long time of sunlight.

Section 8 - Exposure Controls/Personal Protection

Control parameters

CAS No.	ACGIH	NIOSH	OSHA
7429-90-5	TLV-TWA 1mg/m ³	REL-TWA 2mg/m ³ REL-TWA 5mg/m ³ REL-TWA 10mg/m ³	PEL-TWA 5mg/m ³ PEL-TWA 15mg/m ³
24937-79-9	N/A	N/A	N/A
7782-42-5	TLV-TWA 2mg/m ³	REL-TWA 2.5mg/m ³	PEL-TWA 15mppcf PEL-TWA 20mppcf
7440-50-8	TLV-TWA 0.2mg/m ³ TLV-TWA 1mg/m ³	REL-TWA 1mg/m ³ REL-TWA 0.1mg/m ³	PEL-TWA 0.1mg/m ³ PEL-TWA 1mg/m ³
61789-96-6	N/A	N/A	N/A
9002-88-4	N/A	N/A	N/A
9003-07-0	N/A	N/A	N/A
21324-40-3	N/A	N/A	N/A
96-49-1	N/A	N/A	N/A

Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 6 of 11

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

Personal Protective Equipment:

Respiratory protection: Wear suitable protective mask. For a large large number of battery leakages, wear chemical protective clothing, including self-contained breathing apparatus.

Hand Protection: Wear appropriate protective gloves to reduce skin contact.

Eye Protection: Wear safety goggles or eye protection combined with respiratory protection.

Skin and Body Protection: Working environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain hazardous substances in the workplace.

Section 9 - Physical and Chemical Properties

Information on basic physical and chemical properties

Colour:	Blue.
Physical State:	Cylindrical
Odour:	Not available.
Odour threshold:	Not available.
pH:	Not available.
Melting point/freezing point:	Not available.
Initial boiling point and boiling range:	Not available.
Flash Point:	Not available.
Evaporation rate:	Not available.
Flammability (solid, gas):	Not available.
Explosion Limits (vol% in air):	Not available.
Vapour pressure, kPa at 20°C:	Not available.
Vapor density:	Not available.
Density/Relative density (water = 1):	Not available.
Solubility(ies):	Not available.
Partition coefficient: n-octanol/water:	Not available.
Auto-ignition temperature:	Not available.
Decomposition temperature:	Not available.
Viscosity:	Not available.



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 7 of 11

Other information:

Voltage	3.7V
Electric capacity	1000mAh
Electric Energy	3.7Wh

Section 10 - Stability and Reactivity

Reactivity: No data available.**Chemical stability:** Stable.**Possibility of hazardous reactions:** No data available.**Conditions to Avoid:** Flames, sparks, and other sources of ignition, incompatible materials.**Incompatible materials:** Oxidizing agents, acid base.**Hazardous decomposition products:** Carbon monoxide, carbon dioxide, lithium oxide fumes.

Section 11 - Toxicological Information

Acute Toxicity:

CAS No.	LC50/LD50
7429-90-5	No data available.
24937-79-9	No data available.
7782-42-5	No data available.
7440-50-8	No data available.
61789-96-6	No data available.
9002-88-4	No data available.
9003-07-0	No data available.
21324-40-3	No data available.
96-49-1	LD50 Rat (oral): 10g/kg

Skin corrosion/irritation: No data available.**Serious eye damage/irritation:** No data available.**Respiratory or Skin sensitization:** No data available.**Germ Cell mutagenicity:** No data available.**Carcinogenicity:** No data available.**Reproductive toxicity:** No data available.



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 8 of 11

Specific target organ toxicity-Single exposure: No data available.

Specific target organ toxicity-Repeated exposure: No data available.

Aspiration hazard: No data available.

Information on the likely routes of exposure: No data available.

Eye: No data available.

Skin: No data available.

Ingestion: No data available.

Inhalation: No data available.

Section 12 - Ecological Information

Ecological Toxicity: No data available.

Persistence and degradability: No data available.

Bioaccumulative Potential: No data available.

Mobility in Soil: No data available.

Other adverse effects: No data available.

Section 13 - Disposal Considerations

Disposal methods:

Recommendation:

Consult state, local or national regulations to ensure proper disposal.

Uncleaned packaging

Recommendation: Disposal must be made according to official regulations.

Section 14 - Transport Information

UN Number	
IATA	UN3481
IMDG	UN3481
UN Proper shipping name	
IATA	Lithium ion batteries contained in equipment
IMDG	LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT
Transport hazard class(es)	
IATA	9
IMDG	9



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 9 of 11

Packing group	
IATA	N/A
IMDG	N/A
Packaging Sign	
IATA	N/A
IMDG	N/A
Environmental hazards	
Marine pollutant:	No
Special precautions for user	No information available.

Transport information: The Li-ion Battery 14650 has passed the test UN38.3, according to the report ID: MNIP2HUX92592721.

According to the Packing Instruction 967 section II of IATA DGR 60th Edition for transportation.

According to the special provision 188 of IMDG (38-16). The goods are not subject to other provision of this code.

Note: Batteries weight in the package < 5kg. (By air, Batteries installed in equipment)

Transport Fashion: By air, by sea.

Section 15 - Regulatory Information

Safety, health and environmental regulations/legislation specific for the substance or mixture

CAS No.	TSCA	IECSC	DSL/NDL	EINECS/ ELINCS/ NLP
7429-90-5	Listed	Listed	Listed DSL	Listed
24937-79-9	Listed	Listed	Listed DSL	Listed
7782-42-5	Listed	Listed	Listed DSL	Listed
7440-50-8	Listed	Listed	Listed DSL	Listed
61789-96-6	Listed	Listed	Listed DSL	Listed
9002-88-4	Listed	Listed	Listed DSL	Listed
9003-07-0	Listed	Listed	Listed DSL	Listed



21324-40-3	Listed	Listed	Listed DSL	Listed
96-49-1	Listed	Listed	Listed DSL	Listed

Section 16 - Other Information

Issue Time: 2019-06-27

Issue Department: Technical department

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH: (American Conference of Governmental Industrial Hygienists);

NIOSH: (US National Institute for Occupational Safety and Health);

OSHA: (US Occupational Safety and Health);

TLV: (Threshold Limit Value)

TWA: (Time Weighted Average);

STEL: (Short Term Exposure Limit);

PEL: (Permissible Exposure Level);

REL: (Recommended Exposure Limit);

PC-STEL: (Permissible concentration-short time exposure limit);

PC-TWA: (Permissible concentration-time weighted average);

LC50: (Lethal concentration, 50 percent kill);

LD50: (Lethal dose, 50 percent kill);

IARC: (International Agency for Research on Cancer);

EC50: (Median effective concentration);

BCF: (Bioconcentration Factor);

BOD: (Biochemical oxygen demand);

NOEC: (No observed effect concentration);

NTP: (US National Toxicology Program);



Pony Testing International Group

Report No.: MNIZDMWX92683716 Date: 06.27.2019 Page 11 of 11

RTECS: (Registry of Toxic Effects of Chemical Substances);
 IATA: (International Air Transport Association);
 IMDG: (International Maritime Dangerous Goods);
 TDG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations);
 TOC: (Total Organic Carbon);
 TSCA: (Toxic Substances Control Act of USA);
 DSL: (the Domestic Substances List of Canada);
 NDCL: (the Non-domestic Substances List of Canada)

End of report