


FISCHER Bolt type FBN II Steel Zinc plated 8/70 (8X131)



| | |
|----------------|---------------|
| Article number | 63324.080.070 |
| Brand | - |
| UBB | 500504267799 |
| UNSPSC | 31162101 |
| EAN | 4006209407776 |
| PKG. of 20 | Full Box Only |

Technical Parameters

| | |
|-------------------|---------------|
| Diameter | M8 |
| Length | 131 mm |
| Material | Steel |
| Approval | ETA Option 7 |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Type no. | FBN II |

Info

do = Nominal diameter of drill bit.
 tfix = Grip range.
 hef = Effective anchorage depth.
 Min. td = Recommended drilling depth.
 kN = Load in kN.
 The allowable load is valid for one single anchor, at cracked concrete (tensile zone) with concrete class C20/25, incl. partial safety factor $\gamma_f = 1,4$ and if the S_{cr} , N and C_{cr} , N are taken in to account.
 When reduction on spacing and edge distance take place a re-

Standards

calculation of forces should be carried out by making use of the technical guide or calculation software, they are available on request. Final calculations should comply with the complete European Technical Approval (ETA), this approval is also available on request.

Technical Specification

| | |
|---------|--------------|
| d-D | M8 |
| do | 8 |
| hef | 40 |
| kN | 2.9 |
| L (mm) | 131 |
| Min. td | 126 |
| Ring ø | 16 |
| tfix | 70 |
| Type | 8/70 (8X131) |

Technical Drawing

