



**Retaining ring internal, type
NA2 ASME B18.27 Spring
steel UNS G10600/G10900 10
Inch**

Article number	U36050.999.1000
Brand	-
UBB	500626969066
UNSPSC	31162400
EAN	8712423061743
PKG. of 1	Full Box Only

Technical Parameters

Material	Spring steel
Material technical	UNS G10600/ G10900
Info	Warning: electroplating of these products may cause hydrogen embrittlement. During assembly it is essential to not over-compress the rings, a maximum compression of $0,99 \times S1$ is recommended. For proper installation use pliers with spread limiter or assemble with the aid of a cone.


Standards

ASME	B18.27
------	--------

Technical Specification

B	10
Groove G	10.45
Groove W	0.209
Groove Z	0.675
Ring D	10.92

Technical Drawing



Ring E $\approx$ 0.675

Ring T 0.187

Size NA2-1000