



SAFETY DATA SHEET

3302 CombiPrimer Tack-Coat

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

Product name and/or code : 3302 CombiPrimer Tack-Coat
 Rust-Oleum Netherlands BV, PO. Box 138, NL-4700 AC Roosendaal, The Netherlands
 NV Martin Mathys, Kolenbergstraat 23, B-3545 Zelem, Belgium

Emergency phone number : Rust-Oleum: +31(0)165-593636; Fax +31(0)165-593600
 Martin Mathys: +32(0)13-460200; Fax +32(0)13-460201

e-Mail address of person responsible for this SDS : rpmeurohas@ro-m.com

Product use : Paint.

2. HAZARDS IDENTIFICATION

The product is classified as dangerous according to Directive 1999/45/EC and its amendments.

Classification : F; R11
 Xn; R20/21
 Xi; R36/38
 R66
 N; R51/53

Physical/chemical hazards : Highly flammable.

Human health hazards : Harmful by inhalation and in contact with skin. Irritating to eyes and skin. Repeated exposure may cause skin dryness or cracking.

Environmental hazards : Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Substances presenting a health or environmental hazard within the meaning of the Dangerous Substances Directive 67/548/EEC.

| Chemical name | CAS # | % | EU no. | Classification |
|--|------------|---------|-----------|---|
| isoparaffines C8-C10 mixed, boilingrange 115-145 | 90622-56-3 | 25 - 50 | 292-458-5 | F; R11 Xn; R65 Xi; R38 R67 N; R51/53 [1] [2] |
| xylene (mixture of isomeres) | 1330-20-7 | 25 - 50 | 215-535-7 | R10 Xn; R20/21 Xi; R38 [1] [2] |
| ethyl acetate | 141-78-6 | 10 - 25 | 205-500-4 | F; R11 Xi; R36 R66, R67 [1] [2] |
| 1-methoxy-2-propanol | 107-98-2 | 5 - 10 | 203-539-1 | R10 R67 [1] [2] |
| See section 16 for the full text of the R-phrases declared above | | | | |

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

Occupational exposure limits, if available, are listed in section 8.

4. FIRST AID MEASURES

First aid measures

General : In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.

Inhalation : Remove to fresh air. Keep person warm and at rest. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. Give nothing by mouth. If unconscious, place in recovery position and seek medical advice.

Skin contact : Remove contaminated clothing and shoes. Wash skin thoroughly with soap and water or use recognized skin cleanser. Do NOT use solvents or thinners.

Eye contact : Check for and remove any contact lenses. Immediately flush eyes with running water for at least 15 minutes, keeping eyelids open.

Ingestion : If swallowed, seek medical advice immediately and show this container or label. Keep person warm and at rest. Do not induce vomiting.

5. FIRE-FIGHTING MEASURES

- Extinguishing media** : Recommended: alcohol-resistant foam, CO₂, powders, water spray.
Not to be used : water jet.
- Recommendations** : Fire will produce dense black smoke. Exposure to decomposition products may cause a health hazard. Appropriate breathing apparatus may be required. Cool closed containers exposed to fire with water. Do not release runoff from fire to drains or watercourses.
- Hazardous combustion products** : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide

6. ACCIDENTAL RELEASE MEASURES

- Personal precautions** : Exclude sources of ignition and ventilate the area. Avoid breathing vapor or mist. Refer to protective measures listed in sections 7 and 8.
- Spill** : Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see section 13). Do not allow to enter drains or watercourses. Preferably clean with a detergent. Avoid using solvents. If the product contaminates lakes, rivers, or sewers, inform the appropriate authorities in accordance with local regulations.

Note: see section 8 for personal protective equipment and section 13 for waste disposal.

7. HANDLING AND STORAGE

- Handling** : Vapors are heavier than air and may spread along floors. Vapors may form explosive mixtures with air. Prevent the creation of flammable or explosive concentrations of vapors in air and avoid vapor concentrations higher than the occupational exposure limits.
- In addition, the product should only be used in areas from which all naked lights and other sources of ignition have been excluded. Electrical equipment should be protected to the appropriate standard.
- Keep container tightly closed. Keep away from heat, sparks and flame. No sparking tools should be used.
- Avoid contact with skin and eyes. Avoid the inhalation of dust, particulates, spray or mist arising from the application of this preparation. Avoid inhalation of dust from sanding.
- Eating, drinking and smoking should be prohibited in area where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking.
- Put on appropriate personal protective equipment (see section 8).
- Comply with the health and safety at work laws.
- Storage** : Store in accordance with local regulations. Observe label precautions. Do not store above the following temperature: 30°C (86°F). Store in a dry, cool and well-ventilated area. Keep away from heat and direct sunlight.
Keep away from sources of ignition. Keep away from: oxidizing agents, strong alkalis, strong acids.
No smoking. Prevent unauthorized access. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not empty into drains.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

- Engineering measures** : Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and solvent vapors below the OEL, suitable respiratory protection must be worn.

Ingredient name

isoparaffines C8-C10 mixed, boilingrange 115-145

xylene (mixture of isomers)

ethyl acetate

1-methoxy-2-propanol

Occupational exposure limits

EH40/2005 WELs (United Kingdom (UK), 8/2007).

STEL: 850 mg/m³, (as turpentine (150 ppm)) 15 minute(s). Form: Vapor
TWA: 566 mg/m³, (as turpentine (100 ppm)) 8 hour(s). Form: Vapor

EH40/2005 WELs (United Kingdom (UK), 8/2007). Absorbed through skin.

STEL: 441 mg/m³ 15 minute(s).
STEL: 100 ppm 15 minute(s).
TWA: 220 mg/m³ 8 hour(s).
TWA: 50 ppm 8 hour(s).

EH40/2005 WELs (United Kingdom (UK), 8/2007).

STEL: 400 ppm 15 minute(s).
TWA: 200 ppm 8 hour(s).

EH40/2005 WELs (United Kingdom (UK), 8/2007). Absorbed through skin.

STEL: 560 mg/m³ 15 minute(s).
STEL: 150 ppm 15 minute(s).
TWA: 375 mg/m³ 8 hour(s).
TWA: 100 ppm 8 hour(s).

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Exposure controls/personal protection

| | |
|--|--|
| Occupational exposure controls | : Use only with adequate ventilation. Use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. The engineering controls also need to keep gas, vapor or dust concentrations below any lower explosive limits. Use explosion-proof ventilation equipment. |
| Hygiene measures | : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location. |
| Respiratory protection | : Recommended: organic vapor filter (Type AX) . |
| Hand protection | : >8 hours (breakthrough time): Gloves : polyvinyl alcohol (PVA) (EN 374) . 1-4 hours (breakthrough time): Rubber gloves : nitrile rubber (EN 374) . <i>Barrier creams may help to protect the exposed areas of the skin but should not be applied once exposure has occurred. The user must check that the final choice of type of glove selected for handling this product is the most appropriate and takes into account the particular conditions of use, as included in the user's risk assessment.</i> |
| Eye protection | : Recommended: safety glasses with side-shields . |
| Skin protection | : Recommended: Overalls buttoned to the neck and wrist. |
| Environmental exposure controls | : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels. |

9. PHYSICAL AND CHEMICAL PROPERTIES

| | |
|----------------------------------|--|
| Physical state | : Liquid. [Hazy liquid.] |
| Odor | : Characteristic. |
| Color | : Blue. |
| Flash point | : Closed cup: 15°C (59°F) [Setaflash / Tag (ASTM D56)] |
| Boiling point | : >80°C (>176°F) |
| Explosion limits | : Lower: 1% Upper: 12% |
| Vapor pressure | : 10 kPa (75 mm Hg) |
| Vapor density | : >1 [Air = 1] |
| Evaporation rate (BuAc=1) | : 6.2 (Butyl acetate. = 1) |
| Volatility % | : 93.8% (v/v), 94.46% (w/w) |
| Viscosity | : Dynamic: 50 mPa·s (50 cP) |
| Relative density (kg/L) | : 0.829 |

10. STABILITY AND REACTIVITY

Stable under recommended storage and handling conditions (see section 7).

Hazardous decomposition products: carbon monoxide, carbon dioxide, smoke, oxides of nitrogen.

Keep away from the following materials to prevent strong exothermic reactions: oxidizing agents, strong alkalis, strong acids.

11. TOXICOLOGICAL INFORMATION

There is no data available on the preparation itself. The preparation has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and classified for toxicological hazards accordingly. See sections 3 and 15 for details.

Exposure to component solvent vapor concentrations in excess of the stated occupational exposure limit may result in adverse health effects such as mucous membrane and respiratory system irritation and adverse effects on the kidneys, liver and central nervous system. Solvents may cause some of the above effects by absorption through the skin. Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and, in extreme cases, loss of consciousness. Repeated or prolonged contact with the preparation may cause removal of natural fat from the skin, resulting in non-allergic contact dermatitis and absorption through the skin. If splashed in the eyes, the liquid may cause irritation and reversible damage.

Acute toxicity

| Product/ingredient name | Result | Species | Dose | Exposure |
|--|----------------------|---------|---------------------|----------|
| isoparaffines C8-C10 mixed, boilingrange 115-145 | LD50 Dermal | Rabbit | >3000 mg/kg | - |
| | LD50 Oral | Rat | >10000 mg/kg | - |
| | LC50 Inhalation | Rat | 21 g/m ³ | 4 hours |
| | Vapor | | | |
| xylene (mixture of isomeres) | LD50 Intraperitoneal | Rat | 2459 mg/kg | - |
| | LD50 Oral | Rat | 4300 mg/kg | - |
| | LD50 Subcutaneous | Rat | 1700 mg/kg | - |
| | LC50 Inhalation Gas. | Rat | 5000 ppm | 4 hours |

11. TOXICOLOGICAL INFORMATION

| | | | | |
|----------------------|-----------------------|--------|-------------------------|---------|
| ethyl acetate | LC50 Inhalation Vapor | Rat | 5000 ppm | 4 hours |
| | LD50 Dermal | Rabbit | >20 mL/kg | - |
| | LD50 Oral | Rat | 5620 mg/kg | - |
| 1-methoxy-2-propanol | LDLo Subcutaneous | Rat | 5 gm/kg | - |
| | LC50 Inhalation Gas. | Rat | 1600 ppm | 8 hours |
| | LC50 Inhalation Gas. | Rat | >6000 ppm | 6 hours |
| | LD50 Intraperitoneal | Rat | 3720 mg/kg | - |
| | LD50 Oral | Rat | 6600 mg/kg | - |
| | LD50 Subcutaneous | Rat | 7800 mg/kg | - |
| | LDLo Oral | Rat | 3739 mg/kg | - |
| | LC50 Inhalation Vapor | Rat | 55000 mg/m ³ | 4 hours |
| | LC50 Inhalation Gas. | Rat | 10000 ppm | 5 hours |
| | LCLo Inhalation Vapor | Rat | 7000 ppm | 6 hours |

12. ECOLOGICAL INFORMATION

There is no data available on the preparation itself.
Do not allow to enter drains or watercourses.

The preparation has been assessed following the conventional method of the Dangerous Preparations Directive 1999/45/EC and is classified for eco-toxicological properties accordingly. See sections 2 and 15 for details.

Aquatic ecotoxicity

| Ingredient name | Result | Species | Exposure |
|--|--|---|----------|
| isoparaffines C8-C10 mixed, boilingrange 115-145 | Acute EC50 >1 mg/L | Daphnia | 24 hours |
| | Acute IC50 >10 mg/L | Algae | 72 hours |
| | Acute LC50 18.4 mg/L | Fish - Rainbow trout (oncorhynchus mykiss) | 96 hours |
| xylene (mixture of isomeres) | Acute LC50 13500 to 19200 ug/L Fresh water | Fish - Rainbow trout, donaldson trout - Oncorhynchus mykiss - 0.9 g | 96 hours |
| | Acute LC50 13400 ug/L Fresh water | Fish - Fathead minnow - Pimephales promelas - 31 days - 18.4 mm - 0.077 g | 96 hours |
| | Acute LC50 13500 to 16100 ug/L Fresh water | Fish - Bluegill - Lepomis macrochirus - 1.1 g | 96 hours |
| ethyl acetate | Acute LC50 1600000 ug/L Fresh water | Crustaceans - Aquatic sowbug - Asellus aquaticus | 48 hours |
| | Acute LC50 698000 ug/L Fresh water | Daphnia - Water flea - Daphnia magna - <1 days | 48 hours |
| | Acute LC50 484000 to 602000 ug/L Fresh water | Fish - Rainbow trout, donaldson trout - Oncorhynchus mykiss - Juvenile (Fledgling, Hatchling, Weanling) | 96 hours |
| 1-methoxy-2-propanol | Acute LC50 295000 ug/L Fresh water | Daphnia - Water flea - Daphnia pulex - <1 days | 48 hours |
| | Acute LC50 230000 to 250000 ug/L Fresh water | Fish - Fathead minnow - Pimephales promelas - 29 to 30 days - 18.2 mm - 0.106 g | 96 hours |
| | Acute LC50 175000 ug/L Fresh water | Daphnia - Water flea - Daphnia cucullata - 11 days | 48 hours |
| | Acute EC50 >1000 mg/l | Algae - Selenastrum capricornutum | 7 days |
| | Acute LC50 20800 mg/l | Fish - Fathead minnow | 96 hours |
| | Acute LC50 23300 mg/l | Daphnia | 96 hours |

Ecological information

Biodegradability

| Ingredient name | Test | Result | Dose | Inoculum |
|------------------------------|-----------|--------------------------------|-----------------|----------|
| xylene (mixture of isomeres) | - | 90 % - Readily - 5 days | - | - |
| ethyl acetate | OECD 301D | 70 % - Readily - 28 days | - | - |
| 1-methoxy-2-propanol | OECD 301E | 96 % - Readily - 28 days | - | - |
| | - | >90 % - Readily - 5 days | 1.95 gO2/g ThOD | - |
| | OECD 301C | 88 to 92 % - Readily - 28 days | - | - |

Conclusion/Remark : Not available.

| Ingredient name | Aquatic half-life | Photolysis | Biodegradability |
|------------------------------|----------------------|------------|------------------|
| xylene (mixture of isomeres) | - | - | Readily |
| ethyl acetate | - | - | Readily |
| 1-methoxy-2-propanol | Fresh water <28 days | - | Readily |

Bioaccumulative potential

| Ingredient name | LogP _{ow} | BCF | Potential |
|--|--------------------|------|-----------|
| isoparaffines C8-C10 mixed, boilingrange 115-145 | >3 | - | high |
| xylene (mixture of isomeres) | 3.2 | - | high |
| ethyl acetate | 0.7 | - | low |
| 1-methoxy-2-propanol | -0.49 | <100 | low |

13. DISPOSAL CONSIDERATIONS

Do not allow to enter drains or watercourses.
Dispose of according to all federal, state and local applicable regulations.



European waste catalogue (EWC) : The European Waste Catalogue classification of this product, when disposed of as waste, is: 08 01 11* waste paint and varnish containing organic solvents or other dangerous substances. If this product is mixed with other wastes, this code may no longer apply. If mixed with other wastes, the appropriate code should be assigned. For further information, contact your local waste authority.

Hazardous waste : Yes.

14. TRANSPORT INFORMATION

Transport within user's premises: always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

International transport regulations

| Regulatory information | UN number | Proper shipping name | Classes | PG* | Label | Additional information |
|------------------------|-----------|--|---------|-----|--|--|
| ADR/RID Class | 1263 LQ | Paint. Limited quantity | 3 | II | | Limited quantity: LQ7 Remarks: (≤ 5L:) Limited Quantity - ADR/IMDG 3.4 ADR Tunnel Restriction Code: (D/E) |
| IMDG Class | 1263 LQ | Paint. Limited quantity Marine pollutant (isoparaffines C8-C10 mixed, boilingrange 115-145) | 3 | II | | Emergency schedules (EmS): F-E + S-E Marine pollutant (P) Remarks: (≤ 5L:) Limited Quantity - ADR/IMDG 3.4.6 |
| IATA Class | 1263 | Paint. | 3 | II |   | Passenger and Cargo Aircraft Quantity limitation: 60 L Packaging instructions: 309 Cargo Aircraft Only Quantity limitation: 220 L Packaging instructions: 310 Limited Quantities - Passenger Aircraft Quantity limitation: 10 L Packaging instructions: Y 309 |

PG* : Packing group

15. REGULATORY INFORMATION

EU regulations

: The product is classified and labelled for supply in accordance with the Directive 1999/45/EC as follows:

Hazard symbol or symbols



Highly flammable, Harmful, Dangerous for the environment

Risk phrases

: R11- Highly flammable.
R20/21- Harmful by inhalation and in contact with skin.
R36/38- Irritating to eyes and skin.
R66- Repeated exposure may cause skin dryness or cracking.
R51/53- Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases

: S2- Keep out of the reach of children.
S23- Do not breathe vapor.
S29- Do not empty into drains.
S36/37- Wear suitable protective clothing and gloves.
S46- If swallowed, seek medical advice immediately and show this container or label.
S51- Use only in well-ventilated areas.

Contains

: xylene (mixture of isomeres)

VOC for Ready-for-Use Mixture

: IIA/h. Binding primers. EU limit values: 750g/l (2007) 750g/l (2010.)
This product contains a maximum of 741 g/l VOC.

Europe inventory

: All components are listed or exempted.

Other EU regulations

Tactile warning of danger

: Yes, applicable.

CN code

: 3208 20 10

16. OTHER INFORMATION

Full text of R-phrases referred to in sections 2 and 3 - United Kingdom (UK) :

- R11- Highly flammable.
- R10- Flammable.
- R20/21- Harmful by inhalation and in contact with skin.
- R65- Harmful: may cause lung damage if swallowed.
- R36- Irritating to eyes.
- R38- Irritating to skin.
- R36/38- Irritating to eyes and skin.
- R66- Repeated exposure may cause skin dryness or cracking.
- R67- Vapors may cause drowsiness and dizziness.
- R51/53- Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

The information in this Safety Data Sheet is required pursuant to EU Directive 91/155/EEC and its amendments.

Indicates information that has changed from previously issued version.

Notice to reader

The information in this SDS is based on the present state of our knowledge and on current laws. The product is not to be used for purposes other than those specified under section 1 without first obtaining written handling instructions. It is always the responsibility of the user to take all necessary steps to fulfill the demands set out in the local rules and legislation. The information in this SDS is meant to be a description of the safety requirements for our product. It is not to be considered a guarantee of the product's properties. ©Copyright by Rust-Oleum Netherlands B.V. / Martin Mathys B.V.



| | | | |
|----------------------|------------|--------|---------------------|
| Version | 0.02 | v.4.0. | Page: 6/6 |
| Date of issue | 8/09/2009. | | Printed 20/05/2010. |