



**Partially Threaded Hexagon  
Head Structural Bolt  
Assembly, EN 15048, Zinc  
Plated, Class 8.8 M16X110**

Article number	01222.160.110
Brand	-
UBB	500574453196
UNSPSC	31161620
EAN	8715494305952
PKG. of 25	Full Box Only

**Technical Parameters**

Diameter	M16
Length	110 mm
Class	8.8/8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural

**Standards**

ISO	4014/4032
EN	15048

bolting according to EN 15048-1 are compliant with the CPR. Compared to 'common' bolts ISO 4014/4017 (previously DIN 931/933) and nuts ISO 4032 (DIN 934), bolts and nuts according to EN 15048 are additionally marked with 'SB' (Structural Bolting), and the packaging is provided with the CE-mark. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are packaged together in single sealed boxes. A Declaration of Performance (DoP) is available.

## Technical Specification

b (min.): 125mm $L \leq 200$ mm	44
b (min.): $L > 200$ mm	57
b (min.): $L \leq 125$ mm	38
d-D	M16
k	10
L (mm)	110
m (max.)	14.8
P	2
s	24

## Technical Drawing

