

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M8X75

Article number	01400.080.075
Brand	-
UBB	950351187774
UNSPSC	31161620
EAN	8715492408143
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	75 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22

Technical Drawing

d-D	M8
k	5.3
L (mm)	75
P	1.25
s	13

FABORY

