

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised, Class 8.8 M24X200

| | |
|----------------|---------------|
| Article number | 01400.240.200 |
| Brand | - |
| UBB | 950351940347 |
| UNSPSC | 31161620 |
| EAN | 8715492409485 |
| PKG. of 10 | Full Box Only |

Technical Parameters

| | |
|-------------------|--------------------|
| Diameter | M24 |
| Length | 200 mm |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Hot dip galvanized |
| Thread | Metric thread |

Info ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

| | |
|------|------------|
| ISO | 4014 |
| NEN | 1555 |
| NF | E25-112 |
| ASME | B18.2.3.1M |
| DIN | 931 |

Technical Specification

| | |
|---------------------------|----|
| b (min.): 125mmL≤200mm | 60 |
| b (min.): L200mm | 73 |

Technical Drawing

| | |
|---------------------------------|-----|
| b (min.): $L \leq 125\text{mm}$ | 54 |
| d-D | M24 |
| k | 15 |
| L (mm) | 200 |
| P | 3 |
| s | 36 |

