



## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M10X70/S=17

Article No.	01400.100.070
Brand	-
UBB	950351188921
UNSPSC	31161620
EAN	8715492408266
PKG. of 50	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Length (L) (mm)	70
Class	8.8
Driving features	Hexagon
Extra info	ISO metric DIN 931
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width (s) (mm)	17

### Standards

ASME	B18.2.3.1M
ISO	4014
ISO	4014
NEN	1555
DIN	931
NF	E25-112

**Info**  
 ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

b (min.):	32
125mm <math>L \leq 200\text{mm}</math>	
b (min.):	45
$L > 200\text{mm}$	
b (min.):	26
$L \leq 125\text{mm}$	
k	6.4
P	1.50
s	17

**TAPCON** OF COURSE  
SETTING THE STANDARD

