

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M12X55/S=19



Article number	01400.120.055
Brand	-
UBB	950351190497
UNSPSC	31161620
EAN	8715492408495
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	55
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width (s) (mm)	19

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Info
 ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

b (min.): 125mm $L \leq 200\text{mm}$	36
b (min.): $L > 200\text{mm}$	49
b (min.): $L \leq 125\text{mm}$	30
k	7.5
P	1.75
s	19

TARON OF COURSE
SETTING THE STANDARD

