



Structural assembly set ISO metric thread EN 15048 Steel Hot dip galvanized 8.8/8 M10X80

| | |
|----------------|---------------|
| Article number | 01405.100.080 |
| Brand | - |
| UBB | 500574457809 |
| UNSPSC | 31161620 |
| EAN | 8715494311397 |
| PKG. of 100 | Full Box Only |

Technical Parameters

| | |
|-----------------|-----|
| Diameter (d-D) | M10 |
| Length (L) (mm) | 80 |

Standards

| | |
|-----|-----------|
| EN | 15048 |
| ISO | 4014/4032 |

Info

Full boxes only. European constructions must comply with the Construction Products Regulation (CPR) in order to ensure the safety of persons and objects. Generally, construction products according to harmonized European standards (hEN standards) should be used for this purpose. Bolting assemblies for non-preloaded structural bolting according to EN 15048-1 are compliant with the CPR. The manufacturer of the assemblies is CE certified for their production. Bolts and nuts are

packaged together in single sealed boxes. A Declaration of Performance (DoP) is available.

| | |
|--------------------------|--------------------|
| Class | 8.8/8 |
| Driving features | Hexagon |
| Extra info | ISO metric |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Hot dip galvanized |
| Thread | Metric thread |
| Wrench width (s) (mm) | 16 |

Technical Specification

| | |
|---|------|
| b (min.): 125mm $L \leq 200\text{mm}$ | 32 |
| b (min.): $L > 200\text{mm}$ | 45 |
| b (min.): $L \leq 125\text{mm}$ | 26 |
| k | 6.4 |
| m (max.) | 8.4 |
| P | 1.50 |
| s | 16 |

Technical Drawing

