

DIN 931 Partially Threaded Metric Hexagon Head Bolt, Hot Dip Galvanised - Oversized, Class 8.8 M16X240

Article number	01420.160.240
Brand	-
UBB	500621736411
UNSPSC	31161620
EAN	8715494504256
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M16
Length	240 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized bolts and screws are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). oversized

Standards

DIN	931
NF	E25-112
NEN	1555
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 44
125mmL≤200mm

b (min.): L200mm 57

b (min.): L≤125mm 38

d-D M16

k 10

L (mm) 240

P 2

s 24

Technical Drawing

